

Rittal – The System.

Faster – better – everywhere.



IW 6902.670

Enclosure attachment, tilting, top mounting

State: 2025.9.9 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IW 6902.670 - Enclosure attachment, tilting, top mounting

For mounting on IW worktops or other surfaces.



Features

Model No.	IW 6902.670
Product description	With cable tube for protected cable entry.
Applications	For mounting on: IW worktop, prepared for enclosure attachment, surfaces, enclosure attachment/coupling CP-L rectangular 120 x 65 mm, attachment/housing coupling CP 40 (may also be used as tilting adaptor +100°/-60° for CP 40) To fit enclosures up to 20 kg with support arm connection: CP-40, CP-L rectangular 120 x 65 mm, CP-L Ø 130 mm, VESA Standard 75
Material	Sheet steel Concertina section: Plastic
Surface finish	Spray-finished
Colour	RAL 7024
Supply includes	Assembly parts
Tilt angle note	+100°/-60°, adjustable in 7.2° increments via clamping lever and may be limited to +100°/-15° using the stop screw supplied loose.
Tilt angle pitch pattern	7.2 °
OUT_TILT_ANGLE	-60 - 100 °
Packs of	1 pc(s).
Net weight	0.72
Gross weight	0.928

Features

Customs tariff number	73182900
EAN	4028177325791
ECLASS 8.0	27189263

Tender text

Enclosure attachment, tilting, top mounting

For mounting on:

- IW worktop, prepared for enclosure attachment
- CP-L, round
- Surfaces
- Enclosure attachment/coupling CP-L rectangular,
- Attachment/housing coupling CP-S (may also be used as tilting adaptor + 100°/-60° for CP-S)

To fit enclosures up to 20 kg with support arm connection

- CP-S
- CP-L rectangular
- CP-L round
- VESA Standard 75

With cable tube for protected cable entry.