Rittal – The System.

Faster – better – everywhere.



IT 7030.611

CMC III online comfort handle VX

State: 2026.10.30 (Source: www.rittal.com/lt-en)

IT 7030.611 - CMC III online comfort handle VX with master key function for VX, VX IT

Online comfort handle with master key function





Features

Model No.	IT 7030.611
Product description	For door locking, handle lever monitoring and status display. It can be opened directly via a 24 V DC supply voltage or connected to the CMC III or IoT interface via the CMC III Access Control.
Benefits	Remote control and an extensive range of functions for automated access control by linking to the CMC III or IoT interface, e.g. activation via an optional coded lock or transponder reader Optical LED status display of the handle or superordinate CMC III system in the rack Individual activation and colour selection configurable via CMC III or IoT interface Prepared for use of a 40 mm semi-cylinder to DIN 18 252
Material	Die-cast zinc Plastic
Colour	RAL 9005
Supply includes	Comfort handle for profile half-cylinder Connection cable RJ12, 2.9 m Handle adaptor for VX IT aluminium glazed door and VX IT aluminium sheet steel door, vented (door hinge on right/left) Assembly parts

© Rittal 2026

Features

With DC	0.06 A
No. of participating PU compact (max.)	2
No. of participating PU (max.)	16
Number subscribers per PDU note	Max. 5 p. for power supply with PoE
Dimensions	Width: 41 mm Height: 386 mm Depth: 42 mm
To fit	Enclosure type: VX VX IT
Packs of	1 pc(s).
Net weight	1.02 kg
Gross weight	1.039 kg
CRA risk class	Default (Low Risk)
Customs tariff number	83024110
ETIM 9	EC002627
ECLASS 8.0	27189253
Product description	CMC III Online comforthandle VX, RAL9005

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity