

Rittal – The System.

Faster – better – everywhere.



DK 7063.860

Installation kit, depth-variable

State: 2025.8.1 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7063.860 - Installation kit, depth-variable for 482.6 mm (19") component shelf

For 482.6 mm (19") component shelves, in conjunction with L-shaped mounting angles or 482.6 mm (19") mounting frame, infinitely adjustable to the spacing between the two pairs of 482.6 mm (19") mounting angles.

Features

Model No.	DK 7063.860
Product description	In conjunction with L-shaped mounting angles or 482.6 mm (19") mounting frame. Infinitely adjustable to the spacing between the two pairs of 482.6 mm (19") mounting angles. Suitable for all 482.6 mm (19") component shelves in 409 mm width.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	1 set = 2 mounting rails including assembly parts
Load capacity	50 kg
Length	590: 790 mm
Packs of	1 set(s)
Net weight	2.166
Gross weight	2.366
Customs tariff number	83024900
EAN	4028177263253
ECLASS 8.0	27189261

Tender text

Installation kit, depth variable
for 482.6 mm (19 inch) component shelf

2 mounting rails, including assembly parts

Dimensions: 590 - 790 mm

Load capacity: 50 kg

Material: sheet steel, zinc-plated, passivated