

Rittal – The System.

Faster – better – everywhere.



DK 7063.890

Installation kit, depth-variable

State: 2025.12.8 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7063.890 - Installation kit, depth-variable for 482.6 mm (19") component shelf

For 482.6 mm (19") component shelves, in conjunction with L-shaped mounting angles or 482.6 mm (19") mounting frame, infinitely adjustable to the spacing between the two pairs of 482.6 mm (19") mounting angles.

Features

Model No.	DK 7063.890
Product description	In conjunction with L-shaped mounting angles or 482.6 mm (19") mounting frame. Infinitely adjustable to the spacing between the two pairs of 482.6 mm (19") mounting angles. Suitable for all 482.6 mm (19") component shelves in 409 mm width.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	1 set = 2 mounting rails including assembly parts
Load capacity	100 kg
Length	706.5: 1,006.5 mm
Packs of	1 set(s)
Net weight	3.008
Gross weight	3.208
Customs tariff number	83024900
EAN	4028177263260
ECLASS 8.0	27189261

Tender text

Installation kit for component shelf, depth-variable
length 706.5 - 1006.5 mm

2 mounting rails, including assembly parts

Material: Sheet steel, zinc-plated, passivated

Load capacity: 100 kg

Dimensions: 706.5 - 1006.5 mm