
Rittal – The System.

Faster – better – everywhere.



DK 7119.140

Component shelf 1 U, static installation

State: 2026.11.2 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 7119.140 - Component shelf 1 U, static installation 482.6 mm (19") system punchings

482.6 mm (19")/535 mm (metric), support surface for small active components such as modems or mini-hubs in 482.6 mm (19") or metric levels, load capacity: 10 kg.





Features

Model No.	DK 7119.140
Design	482.6 mm (19") version
Product description	The ideal support surface for small active components such as modems or mini-hubs.
Material	Sheet steel
Colour	RAL 7035
Load capacity	10 kg surface load, static
Note	Not suitable for combination with telescopic slides. Free installation height inside the U approx. 35 mm
Dimensions	Width: 482.6 mm Depth: 140 mm
Units	1 U
Packs of	1 pc(s).
Net weight	0.781 kg
Gross weight	0.881 kg

Features

PCF per pack (cradle-to-gate)	3.2 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Component shelf, WHD: 482,6x1 Ux140 mm, 10 kg, static, distance between levels:, static installation, For 482.6 mm (19") system punchings, RAL 7035

Tender text

482.6 mm (19 inch) single-level component shelf,
D: 140 mm

Load capacity: 10 kg surface load, static
Material: Sheet steel, spray finished in RAL 7035