

Rittal – The System.

Faster – better – everywhere.



DK 7163.560 Cable support

State: 2026.6.4 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7163.560 - Cable support hinged, with anti-kink device and clamp

Kink-free cable routing in the central part via mobile chain links, the attachment may be released on both sides, thanks to clamps.



Features

| | |
|-------------------------------|--|
| Model No. | DK 7163.560 |
| Product description | For secure routing of connection cables from the component shelf to the clamping point. Kink-free cable routing in the central part via mobile chain links. The attachment may be released on both sides thanks to clamps. |
| Material | Sheet steel, zinc-plated Centre part: Plastic |
| Supply includes | Assembly parts |
| Note | Max. depth of component shelves = Enclosure depth - 200 mm. |
| To fit | Depth: ≤ 600 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.55 kg |
| Gross weight | 0.712 kg |
| PCF per pack (cradle-to-gate) | 2.4 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |

Features

| | |
|---------------------|--|
| ETIM 9 | EC000322 |
| ECLASS 8.0 | 27400604 |
| Product description | DK Cable support, kink-free, For D: ? 600 mm, Max. depth component shelf = depth rack-200 mm |

Tender text

Kink-free cable support
for enclosures smaller than 600 mm
Material: Sheet steel, zinc-plated, passivated