

Rittal – The System.

Faster – better – everywhere.



TE 7526.834 Module plates

State: 2026.6.5 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TE 7526.834 - Module plates for TE

The base area of the TE may be varied as required using the module plates.

Features

| | |
|-----------------------|--|
| Model No. | TE 7526.834 |
| Design | Vented |
| Product description | The base area of the TE may be varied as required using the module plates. |
| Applications | Please note when selecting suitable gland plates: Enclosure width minus 150 mm Enclosure depth minus 50 mm |
| Material | Sheet steel, zinc-plated |
| Supply includes | Assembly parts |
| Dimensions | Width: 650 mm Depth: 200 mm |
| To fit | Enclosure type: TE Width: 800 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.82 kg |
| Gross weight | 1.02 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | TE Module plate, WxD: 650x200 mm, Vented, For W: 800 mm |

Tender text

Vented module plate

650 mm wide module plate, 200 mm deep module plate

Material: Sheet steel, zinc-plated