

# Rittal – The System.

Faster – better – everywhere.



## DK 7644.000

## Wall-mounted enclosures AE

State: 2025.8.24 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7644.000 - Wall-mounted enclosures AE with 482.6 mm (19") pull-out frame

Wall-mounted enclosure for small networks with pull-out 482.6 mm (19") mounting level and gland plate with brush strip for cable entry at the bottom. Protection category IP 54.

## Features

Model No.	DK 7644.000
Design	with 482.6 mm (19") pull-out frame
Material	Enclosure: Sheet steel Viewing window: Single-pane safety glass, 3 mm
Surface finish	Enclosure: Powder-coated Pull-out frame: Stainless steel
Colour	RAL 7035
Supply includes	Enclosure with hinged door Cam lock with 3 mm double-bit insert Gland plate with brush strip for cable entry in the enclosure base Pull-out frame attached to telescopic slides Outlet filter in enclosure base and on left-hand side Viewing window on right-hand side Cable clamp rail on rear wall Additional cable clamp rail for mounting on the pull-out frame
Dimensions	Width: 600 mm Height: 600 mm Depth: 350 mm
Installation height for components	10 U
Installation height U mounting frame vertical	4 U
Door hinge position	left
Number of locks	2
Basic material	Sheet steel
Protection category to IEC 60 529	IP 54 in conjunction with gland plate for cable gland

# Features

Packs of	1 pc(s).
Net weight	25.175
Gross weight	26.5
Customs tariff number	94032080
EAN	4028177187146
ECLASS 8.0	27142408

# Approvals

Approvals	Lloyds Register of Shipping
-----------	-----------------------------

# Tender text

Wall-mounted distributor enclosure with 482.6 mm (19") pull-out frame

## Enclosure:

Wall-mounted distributor with sheet steel front door, including two cam locks and double-bit lock inserts, a gland plate with cable entry brush strips fitted at bottom, outlet filters fitted at the right of the base and top left of the side panel, fan expansion kit can be fitted as an optional upgrade, a combi-rail with cable clamping hammer-heads as well as a cable clamping rail for attaching to the pull-out frame at the rear, a viewing window fitted in the right side, a pull-out frame mounted on telescopic rails with a 482.6 mm (19") mounting level, 10 U, horizontally and vertically at the front and a 482.6 mm (19") mounting level, 4 U, vertically fitted at the side.

## Material:

Wall section, enclosure cover, front door made from sheet steel, 3 mm single-pane viewing window

## Surface finish:

Enclosure: electrophoretic dipcoat, spray finished, RAL 7035

Pull-out frame: stainless steel.

## Dimensions (W x H x D):

600 x 600 x 350 mm / (4 / 10 U)