Rittal - The System.

Faster – better – everywhere.





DK 7721.535 Wall-mounted enclosures EL, 3-part

State: 2025.11.19 (Source: rittal.com/lt-en)



DK 7721.535 - Wall-mounted enclosures EL, 3-part preconfigured with mounting angles, depth-variable

Wall-mounted enclosure 3-part, pre-configured with: Solid gland plate, top, with brush strip at the bottom, mounting rails, C rails, outlet filter, earth rail, wall-mounting bracket

Features

Model No.	DK 7721.535	
Design	Wall-mounted enclosures IT pre-configured with mounting angles, depth-variable	
Product description	Wall-mounted enclosure with optimum accessibility due to hinged part.	
Material	Wall and hinged part: Sheet steel, 1.5 mm Viewing window: Single-pane safety glass, 3 mm	
Surface finish	Powder-coated	
General colour	RAL 7035	
Colour	Wall and hinged part: RAL 7035 Glazed door: RAL 7035/7015 (slate grey)	
Supply includes	Wall section with solid gland plate at the top and brush strip at the bottom, two vertical mounting rails and C rail, horizontal, for cable clamping Hinged part with 25 mm pitch pattern of holes in the front and rea frame, two 482.6 mm (19") mounting angles at the front, infinitely depth-variable, and side outlet filters on the left and right Earth rail with star earthing Designer glazed door 1 double-kit key no. 5 Wall mounting bracket, 10 mm, reinforced Comfort handle for lock inserts and 2-point locking Security lock 3524 E	
Units	21 U	

© Rittal 2025 2

Features

Dimensions	Width: 600 mm Height: 1,012 mm Depth: 673 mm	
Installation depth	620 mm	
Clearances	Clearance width: 502 mm Clearance height: 949 mm	
Depth hinged part	516 mm	
Depth of wall section	135 mm	
IK Code	IK08	
Load capacity of hinged part (static)	750 N	
Basic material	Sheet steel	
Protection category to IEC 60 529	IP 54 in conjunction with solid gland plate top and bottom	
Packs of	1 pc(s).	
Net weight	57	
Gross weight	59	
Customs tariff number	94032080	
EAN	4028177551039	
E-Number Sweden	E7239962	
ETIM 9	EC000261	
ECLASS 8.0	27142408	

Approvals

Approvals	UL + C-UL (listed)	
Approvaio	oz : o oz (noted)	

© Rittal 2025 3