

# Rittal – The System.

Faster – better – everywhere.



## DK 7824.120

### Side panel, lockable

State: 2025.8.23 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7824.120 - Side panel, lockable for TS, TS IT

Side panel, lockable, sheet steel, for TS.



## Features

|                       |   |
|-----------------------|---|
| Model No.             | DK 7824.120   |
| Product description   | Simply locate from above. Lock with security lock no. 3524 E. Earthing bolt with contact track. |
| Material              | Sheet steel   |
| Surface finish        | Spray-finished  |
| Colour                | RAL 7035  |
| Supply includes       | 2 side panels each with 4 security locks no. 3524 E   |
| To fit                | Enclosure type: TS<br>TS IT<br>Height: 1,200 mm<br>Depth: 1,000 mm                              |
| Basic material        | Sheet steel   |
| Packs of              | 2 pc(s).  |
| Net weight            | 28.6  |
| Gross weight          | 29.8  |
| Customs tariff number | 94039910  |
| EAN                   | 4028177330672   |
| E-Number Sweden       | E7239565  |
| ETIM 9                | EC002524  |

# Features

---

ECLASS 8.0

27182101

## Tender text

Side panel, plug-type for TS

H x D = 1200 x 1000 mm, RAL 7035

Side panel fitted with a T-lock.

Material: Sheet steel, spray finished in RAL 7035

For 1200 mm x 1000 mm enclosures