

# Rittal – The System.

Faster – better – everywhere.



## DK 7824.222

### Glazed door, vented

State: 2026.3.18 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7824.222 - Glazed door, vented for TS, TS IT, VX SE

To replace existing doors. With 180° hinges and swivel handle with security lock no. 3524 E.

## Features

|                       |                                                                                                                                 |
|-----------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Model No.             | DK 7824.222                                                                                                                     |
| Product description   | Surface perforated on both sides with air inlet openings > 78% for optimum air throughput.                                      |
| Material              | Door: Sheet steel<br>Viewing window: Single-pane safety glass, 3 mm                                                             |
| Surface finish        | Powder-coated                                                                                                                   |
| Colour                | RAL 7035                                                                                                                        |
| Supply includes       | Glazed door, vented<br>Comfort handle for profile half-cylinders with security lock 3524 E<br>180° hinges (4)<br>Assembly parts |
| Assembly instruction  | For TS enclosure suites with sheet steel doors, only the 180° hinge 7824.520 may be used.                                       |
| To fit                | Enclosure type: TS<br>TS IT<br>SE<br>Width: 800 mm<br>Height: 2,200 mm                                                          |
| Packs of              | 1 pc(s).                                                                                                                        |
| Net weight            | 22 kg                                                                                                                           |
| Gross weight          | 22.6 kg                                                                                                                         |
| Customs tariff number | 94039910                                                                                                                        |
| ETIM 9                | EC000747                                                                                                                        |
| ECLASS 8.0            | 27182204                                                                                                                        |
| Product description   | DK-TS Glazed door, WxH: 800x2200 mm, Vented                                                                                     |

# Tender text

Glazed door, vented, for TS

Glazed door, vented, made from 1.5 mm sheet steel  
with side slotted surfaces in RAL 7035,  
with foamed-in seal, 180° hinges,  
3 mm thick single-pane safety glass, 4-point latch  
locking rod, comfort handle with security lock no.  
3524 E. A semi-cylinder (40/45 mm) to DIN 18254  
may be inserted.

Hinges with captive hinge pins,  
door hinge may be swapped from right to left without  
dismantling locking rods. Door opening angle 180°.

Material: Sheet steel

Pane: Safety glass, 3 mm

Colour:

Frame: RAL 7035

Pane: Tinted, parsol grey

Dimensions: For enclosures (WxH): W: 800 mm H: 2200 mm