


Rittal – The System.

Faster – better – everywhere.



DK 7824.282

Sheet steel glazed door, vertically divided

State: 2026.4.5 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7824.282 - Sheet steel glazed door, vertically divided for TS 8

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.

Features

| | |
|-------------------------------------|---|
| Model No. | DK 7824.282 |
| Product description | With underlaid viewing panel, 4-point locking rod and comfort handle for profile half-cylinders with security lock 3524 E. The divided design allows room-optimised siting of the enclosures coupled with the best possible access, thanks to a reduced distance between the individual bayed enclosure suites. Max. door opening angle thanks to pre-integrated 180° hinges. |
| Material | Frame: Sheet steel Viewing window: Single-pane safety glass, 3 mm |
| Surface finish | Powder-coated |
| Colour | RAL 7035 |
| Supply includes | Assembly parts |
| Note | Height 2200 mm cannot be combined with swing frame 45 U. |
| IP protection category to IEC 60529 | IP 55 |
| To fit | Enclosure type: TS 8 Width: 800 mm Height: 2,200 mm |
| Packs of | 1 pc(s). |
| Net weight | 37.6 kg |
| Gross weight | 37.6 kg |
| Customs tariff number | 94039910 |
| ECLASS 8.0 | 27182204 |

Tender text

Sheet steel glazed door, vertically divided for TS
With underlaid viewing panel, 4-point locking rod
and comfort handle for semi-cylinder with security
lock 3524 E. Max. door opening angle 180°.

Note:

Cannot be combined with swing frame 45 U.

Material: Sheet steel, viewing window
toughened safety glass 4 mm

Colour: RAL 7035

For enclosures (W x H): 800 x 2200 mm