

Rittal – The System.

Faster – better – everywhere.



DK 7826.786

Roof plate, vented

State: 2025.7.21 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7826.786 - Roof plate, vented for TS, TS IT

In exchange for the standard roof, with and without cable entry.



Features

Model No.	DK 7826.786
Design	One-piece without cable entry
Product description	In exchange for the standard roof. 72 mm high roof plate, all-round vent slots, clamp strip for cable entry. The two-piece design with cable entry allows convenient retrofitting.
Material	Sheet steel
Colour	RAL 7035
To fit	Enclosure type: TS TS IT Width: 800 mm Depth: 600 mm
Packs of	1 pc(s).
Net weight	6.904
Gross weight	7.267
Customs tariff number	73269098
EAN	4028177345621
ETIM 9	EC000744
ECLASS 8.0	27182405

Tender text

DK-TS vented roof plate, W x D = 800 x 600 mm

Material: Sheet steel, spray finished in RAL 7035

Dimensions (W x H x D): 800 mm x 0 mm x 600 mm