


**Rittal – The System.**

Faster – better – everywhere.



# DK 7828.061

## Cable clamp rail

State: 2025.7.27 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7828.061 - Cable clamp rail for TS, TS IT

The cables may be attached to the cable clamp rails with cable ties or nylon tapes, the cable clamp rails are simply located onto the frame section and may additionally be secured with a screw.

## Features

|                       |   |
|-----------------------|---|
| Model No.             | DK 7828.061   |
| Design                | for the inner attachment level  |
| Product description   | For cable routing on the enclosure frame. The cables may be attached to the cable clamp rails with cable ties or nylon loops. The cable clamp rails are easily located onto the frame section of the enclosure frame or mounting frame, and may additionally be secured with a screw. |
| Applications          | On the TS frame<br>between the mounting angles of the TS IT in the enclosure depth  |
| Material              | Sheet steel   |
| Surface finish        | Zinc-plated   |
| Supply includes       | Assembly parts  |
| To fit                | Enclosure type: TS<br>TS IT<br>Width: 600 mm<br>Depth: 600 mm   |
| Packs of              | 4 pc(s).  |
| Net weight            | 0.976   |
| Gross weight          | 1.14  |
| Customs tariff number | 73269098  |
| EAN                   | 4028177235069   |
| ETIM 9                | EC000322  |
| ECLASS 8.0            | 27400604  |

# Tender text

Cable clamp rail for TS 8 inner mounting level

Material: Sheet steel, zinc-plated, passivated

For enclosure dimensions: W: 600 mm D: 600 mm