Rittal – The System.

Faster – better – everywhere.



DK 7856.027

Connection cable

State: 2026.10.31 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 7856.027 - Connection cable for PSM rail

Preassembled connection cable for the Power System Module.

Features

Model No.	DK 7856.027
Design	Single-phase
Connector (type)	IEC 320 connector C14
Rated current (max.)	10 A
Dimensions	Length: 3 m
Sockets	Wago X-Com
Packs of	1 pc(s).
Net weight	0.34 kg
Gross weight	0.389 kg
Customs tariff number	85444290
ETIM 9	EC001576
ECLASS 8.0	27060402
Product description	DK Connection cable, L: 3 m, 10 A, 1-phase, Wago X-Com, C14, For PSM

Tender text

Single-phase UPS connection cable for operating
a PSM busbar with an UPS.
3m, fully wired ready for connection with
adaptor for PSM and IEC 320 C14 connector
(non-heating appliances)
230V/10A

© Rittal 2026