

Rittal – The System.

Faster – better – everywhere.



DK 7955.510

PDU UK, basic version

State: 2025.8.22 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7955.510 - PDU UK, basic version

The compact design allows fast assembly in the zero-U space of TS IT network and server enclosures. Input with CEE connector (16 A/32 A) with BS 1363 (UK) outputs. Distribution output from 3.7 kW to 22 kW.

Features

Model No.	DK 7955.510
Product description	Robust, compact basic power distributor for the IT environment. Thanks to the compact PDU, any IT rack is easily equipped with a professional power distribution system. The TS IT rack even supports tool-free assembly. The compact design allows simple assembly.
Material	Aluminium section, black anodised
Dimensions	Width: 44 mm Depth: 62 mm Length: 440 mm
No. of sockets and type	6 x C13 / 1 x C19
Sockets	6 x GB (type G, BS 1363)
Rated current (max.)	13 A
Infeeds	Qty.: 1 Phases per infeed: 1~
Length of connection cable	3 m
Type of electrical connection	UK
Operating temperature range	0 °C...45 °C
Ambient humidity (non-condensing)	10...95 %
Storage temperature range	-25 °C...70 °C
To fit	Enclosure type: TS IT: ≤ 800 mm
Packs of	1 pc(s).
Net weight	1.24

Features

Gross weight	1.42
Customs tariff number	85366990
EAN	4028177685024
ECLASS 8.0	27142604