Rittal – The System.

Faster – better – everywhere.



# VX 8106.245

# Side panel, screw-fastened, sheet steel

State: 2026.11.14 (Source: www.rittal.com/lt-en)

# VX 8106.245 - Side panel, screw-fastened, sheet steel for VX

Side panels, screw-fastened, sheet steel, for VX.



## Features

| | |
|---|---|
| Model No. | VX 8106.245 |
| Benefits | Time-saving assembly thanks to clip-in side panel holder<br>Automatic potential equalisation and higher EMC protection, thanks to enclosure panel holders with earthing inserts located on the inside<br>Easy positioning in the height and depth with the location aid<br>One-person assembly<br>Earthing bolts with large, paint-free contact surface for optimum contact |
| Material | Sheet steel, 1.5 mm |
| Surface finish | Dipcoat-primed, powder-coated on the outside |
| Colour | RAL 7035 |
| Supply includes | Assembly parts |
| To fit | Enclosure type: VX<br>Height: = 2,000 mm<br>Depth: = 600 mm |
| IP protection category to IEC 60 529 | IP 55<br>IP 66 |

# Features

| | |
|---|---|
| Type rating to 508A | Type 1<br>Type 3R<br>Type 4<br>Type 12 |
| Basic material | Sheet steel |
| Packs of | 2 pc(s). |
| Net weight | 26 kg |
| Gross weight | 29 kg |
| PCF per pack (cradle-to-gate) | 86.73 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94039910 |
| ETIM 9 | EC002524 |
| ECLASS 8.0 | 27182101 |
| Product description | VX Side panel, screw-fastened, for HD: 2000x600 mm, sheet steel |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |
| Explanations | PCF-declaration |