

Rittal – The System.

Faster – better – everywhere.



VX 8126.245

Side panel, screw-fastened, sheet steel

State: 2026.2.14 (Source: [ittal.com/lt-en](https://www.ittal.com/lt-en))



VX 8126.245 - Side panel, screw-fastened, sheet steel for VX

Side panels, screw-fastened, sheet steel, for VX.

Features

Model No.	VX 8126.245
Benefits	<p>Time-saving assembly thanks to clip-in side panel holder</p> <p>Automatic potential equalisation and higher EMC protection, thanks to enclosure panel holders with earthing inserts located on the inside</p> <p>Easy positioning in the height and depth with the location aid</p> <p>One-person assembly</p> <p>Earthing bolts with large, paint-free contact surface for optimum contact</p>
Material	Sheet steel, 1.5 mm
Surface finish	Dipcoat-primed, powder-coated on the outside
Colour	RAL 7035
Supply includes	Assembly parts
To fit	<p>Enclosure type: VX</p> <p>Height: = 2,200 mm</p> <p>Depth: = 600 mm</p>
IP protection category to IEC 60 529	IP 55
Type rating to UL 50E	Type 1 Type 12
Basic material	Sheet steel
Packs of	2 pc(s).
Net weight	32.08
Gross weight	32.6
PCF per pack (cradle-to-gate)	124.2 kg CO ₂ eq (Cat B)

Features

Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
EAN	4028177827547
ETIM 9	EC002524
ECLASS 8.0	27182101

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------