### Rittal - The System.

Faster - better - everywhere.





TS 8612.070

# TS punched section with mounting flange, 17 x 73 mm

State: 2025.11.5 (Source: rittal.com/lt-en)



## TS 8612.070 - TS punched section with mounting flange, $17 \times 73 \text{ mm}$

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.





#### **Features**

Model No.	TS 8612.070
Design	For mounting on doors
Product description	For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Length	690 mm
To fit door width	800 mm
Installation options	On the vertical TS, VX SE enclosure section: On the inner mounting level, height-offset all-round On the horizontal VX SE enclosure section, top in the depth In TP via rail for interior installation: In the width, for inner mounting level As a mounting kit for component shelves in TS, VX SE, simply locate and secure
Assembly instruction	The rail for internal mounting is required when installing in TP

© Rittal 2025

### **Features**

To fit	Enclosure type: VX SE
	TP
	PC
	IW
Packs of	4 pc(s).
Net weight	2.96
Gross weight	3.158
Customs tariff number	73269098
EAN	4028177690318
ETIM 9	EC002625
ECLASS 8.0	27189234

© Rittal 2025 3