Rittal - The System.

Faster – better – everywhere.





TS 8612.120

TS punched section with mounting flange, 17 x 73 mm

State: 2025.11.26 (Source: rittal.com/lt-en)



TS 8612.120 - TS punched section with mounting flange, $17 \times 73 \text{ mm}$

For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.



Features

Model No.	TS 8612.120
Design	For the outer mounting level
Product description	For universal skeleton structures or partial assembly. Simply locate into the punchings and secure.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly screws
Length	1,140 mm
Installation options	On the vertical TS, VX SE enclosure section: On the inner mounting level, height-offset all-round
	On the horizontal VX SE enclosure section, top in the depth
	In TP via rail for interior installation: In the width, for inner mounting
	level
	As a mounting kit for component shelves in TS, VX SE, simply locate and secure
Assembly instruction	The rail for internal mounting is required when installing in TP

© Rittal 2025

Features

To fit	Enclosure type: VX SE
	TP
	PC
	IW
	To fit width/depth: 1,200 mm
Packs of	4 pc(s).
Net weight	4.876
Gross weight	5.133
Customs tariff number	73269098
EAN	4028177212121
ETIM 9	EC002625
ECLASS 8.0	27189234

© Rittal 2025 3