

Rittal – The System.

Faster – better – everywhere.



TS 8612.680

TS punched sections without mounting flanges, 45 x 88 mm

State: 2025.9.8 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8612.680 - TS punched sections without mounting flanges, 45 x 88 mm

Heavy top-mounted equipment mounted directly on the internal surfaces (e.g. roof) is supported. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine.



Features

| | |
|-----------------------|---|
| Model No. | TS 8612.680 |
| Design | for the inner mounting level |
| Product description | Heavy top-mounted equipment mounted directly on the internal surfaces (e.g. roof) is supported. Mounted on the side or rear, the enclosure can then be screw-fastened securely to the machine. The twin profile with 11 rows of holes offers numerous additional opportunities for interior installation. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Installation options | On the vertical and horizontal TS, VX SE enclosure section |
| To fit | Enclosure type: the inner mounting level To fit width/depth: 800 mm |
| Packs of | 2 pc(s). |
| Net weight | 3.638 |
| Gross weight | 3.837 |
| Customs tariff number | 73269098 |

Features

| | |
|------------|---------------|
| EAN | 4028177267077 |
| ETIM 9 | EC002625 |
| ECLASS 8.0 | 27189234 |