

Rittal – The System.

Faster – better – everywhere.



VX 8618.040 Glazed door

State: 2026.7.8 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8618.040 - Glazed door for VX

Instead of a sheet steel door or rear panel.

Features

Model No.	VX 8618.040
Product description	Instead of a sheet steel door or rear panel.
Material	Frame: Extruded aluminium section Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	Frame: RAL 7035 Viewing window (printed mask on the inside): RAL 9005
Supply includes	Glazed door Locking rod with double-bit insert 180° hinges (4)
IK Code	IK08
Note	Lock components for frame 8618.110 are required when mounting instead of the rear panel
Type rating to UL 50E	Type 1 Type 12
IP protection category to IEC 60529	IP 55
To fit	Enclosure type: VX Width: = 600 mm Height: = 2,200 mm
Packs of	1 pc(s).
Net weight	14.6 kg
Gross weight	15.4 kg
Customs tariff number	94039910
ETIM 9	EC000747
ECLASS 8.0	27182204

Features

Product description	VX Glazed door, for WH: 600x2200 mm
---------------------	-------------------------------------

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------

Certificates	Protection category
--------------	---------------------