

Rittal – The System.

Faster – better – everywhere.



VX 8620.082

Base/plinth trim panels, side, 200 mm, stainless steel

State: 2026.6.6 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8620.082 - Base/plinth trim panels, side, 200 mm, stainless steel for base/plinth system VX

Stainless steel base/plinth trim panels are used in the depth to finish off a base/plinth unit at the sides.

Features

Model No.	VX 8620.082
Product description	To finish off a base/plinth unit at the sides and for additional stabilisation or for the interior configuration of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.
Material	Stainless steel 1.4301 (AISI 304)
Surface finish	Brushed, grain 400
Supply includes	Assembly parts
Note	Components from the 1st generation base/plinth system cannot be combined with components from the 2nd generation base/plinth system
Dimensions	Height: 200 mm
To fit	Depth: = 600 mm
Type rating to UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12
Weight/pack	4.5 kg
Packs of	2 pc(s).
Net weight	2.94 kg
Gross weight	3.08 kg
Customs tariff number	94039910
ETIM 9	EC000721

Features

ECLASS 8.0

27182003

Product description

VX Base/plinth trim panel, side, H: 200 mm, for D: 600 mm, stainless steel, 1.4301

Approvals

Approvals

UL + C-UL - FTTA