Rittal – The System.

Faster – better – everywhere.



# VX 8640.033

# Base/plinth trim panels, side, 100 mm

State: 2026.11.22 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# VX 8640.033 - Base/plinth trim panels, side, 100 mm for base/plinth system VX, sheet steel

To finish off a base/plinth unit at the sides and for additional stability, or for the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.

## Features

| | |
|---|---|
| Model No. | VX 8640.033 |
| Product description | To finish off a base/plinth unit at the sides and for additional stability, or for the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths. |
| Material | Sheet steel |
| Colour | RAL 9005 |
| Supply includes | Assembly parts |
| Dimensions | Height: 100 mm |
| To fit | Enclosure type: VX<br>TX CableNet<br>Depth: = 600 mm |
| Type rating to 508A | Type 1, 12 |
| Weight/pack | 1.78 kg |
| Packs of | 2 pc(s). |
| Net weight | 1.65 kg |
| Gross weight | 1.73 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000721 |
| ECLASS 8.0 | 27182003 |
| Product description | VX Base/plinth trim panel, side, H: 100 mm, for D: 600 mm, sheet steel |

© Rittal 2026

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL - FTTA |