

Rittal – The System.

Faster – better – everywhere.



PC 8800.920

Base/plinth, stationary

State: 2026.5.22 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PC 8800.920 - Base/plinth, stationary for PC, IW

Design-coordinated with the enclosures, height 100 mm, with front projection.

Features

| | |
|-------------------------------|--|
| Model No. | PC 8800.920 |
| Product description | Design-coordinated with the enclosures, with front projection. |
| Material | Sheet steel, 2.0 mm |
| Colour | RAL 7035 Design component, front: RAL 7015 |
| Supply includes | 1 design component, front 1 base/plinth component, rear 2 base/plinth trim panels, side |
| Dimensions | Height: 100 mm |
| To fit | Enclosure type: PC IW Width: = 600 mm Depth: = 600 mm |
| Suitable for depth | 600 mm |
| Packs of | 1 pc(s). |
| Net weight | 11.92 kg |
| Gross weight | 13.02 kg |
| PCF per pack (cradle-to-gate) | 49.5 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000721 |
| ECLASS 8.0 | 27182003 |
| Product description | PC Base/plinth, stationary, for PC, IW, for D: 600 mm, H: 100 mm, Sheet steel |