

Rittal – The System.

Faster – better – everywhere.



SV 9340.000

Busbar support

State: 2026.2.2 (Source: ittal.com/lt-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9340.000 - Busbar support for flat copper busbars

For flat copper bars up to 800 A.

Features

Model No.	SV 9340.000
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Rated operating voltage	1000 V, 3~
Note on Model No.	If 12 x 5/10 mm busbars are used, spacer 9340.090 is additionally required
Number of poles	3-pole
Internal attachment	Yes
Centre-to-centre spacing of busbars	60 mm
To fit busbars	12 x 5 - 30 x 10
Packs of	4 pc(s).
Net weight	0.724
Gross weight	0.732
Customs tariff number	85469010
EAN	4028177502321
ETIM 9	EC001166
ECLASS 8.0	27400607

Approvals

Approvals

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

RiLine60 busbar support, 3-pole

Busbar support with internal attachment, 3-pole

Technical specifications

Bar centre distance: 60 mm

Busbars E-Cu: 12 x 5/10, 15 x 5 to 30 x 10 mm

Construction width: 20 mm

Length: 190 mm

System:

Rittal RiLine60