


Rittal – The System.

Faster – better – everywhere.



SV 9340.820

Twin cord

State: 2025.8.4 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.820 - Twin cord for OM adaptors with spring terminal block 2.5 – 16 mm²

Pre-assembled connection cables for individual connection of up to two switchgear units per adaptor.



Features

Model No.	SV 9340.820
Product description	Pre-assembled connection cables for individual connection of up to two switchgear units per adaptor.
Material	PVC insulation Temperature resistant to 105 °C Wire ends with ultrasonic wire-end compression at both ends
AWG	AWG 10 = 5.26 mm ² ÷ 6 mm ²
Note	AWG = American Wire Gauge
Dimensions	Length: 140 mm, 250 mm
Packs of	6 pc(s).
Net weight	0.138
Gross weight	0.16
Copper weight (kg per piece)	0.013
Customs tariff number	85444290
EAN	4028177583573
ETIM 9	EC000839
ECLASS 8.0	27400613

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK