

Rittal – The System.

Faster – better – everywhere.



SV 9345.005 Fuse holders

State: 2026.5.29 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.005 - Fuse holders 31 A to 60 A

Fuse holders up to 60 A, 3-pole. Simple mounting on support rails or via OM component adaptors on busbars.

Features

Model No.	SV 9345.005
Design	For category CC fuse type
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Connection for round conductor	AWG 8 - 18
Type of electrical connection	Box terminal
For fuse type (class)	CC
Rated operating current max.	30 A
Rated operating voltage	600 V, 3~
Fuse standard	UL 248-4
Note	For snap-on mounting on 35 mm (7.5 mm/15 mm high) support rails to DIN EN 60 715 or RiLine component adaptor combinations (OM adaptors/supports)
Test specification	UL 4248-1 UL 4248-4 UL 4248-8
Note on Model No.	Not suitable for accommodating fuses 10 x 38 mm to IEC 60 269-2/-4/-6
Dimensions	Width: 54 mm Height: 81 mm
Connection of round conductors	0.75 - 25 mm ²
To fit fuses	Diameter: 10 mm Length: 38 mm

Features

Voltage range for indicator lights	110 - 600 V
Electrical ratings UL (SCCR)	200 kA - 600 V, Fuse Class CC max. 30 A, JDDZ/7
Number of poles	3-pole
Round conductor cross-section	0.75 - 25 mm ²
Packs of	4 pc(s).
Net weight	0.4 kg
Gross weight	0.634 kg
Copper weight (kg per piece)	0.018
Customs tariff number	85369095
ETIM 9	EC001644
ECLASS 8.0	27400613
Product description	SV Fuseholder, Class CC, 30 A, 600 V, 3-pole, (60 mm)

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK