

# Rittal – The System.

Faster – better – everywhere.



## SV 9346.015 NH slimline fuse-switch disconnecter

State: 2024.5.21 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9346.015 - NH slimline fuse-switch disconnecter with electronic fuse monitoring

## Features

|                                               |                                                                                                                           |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|
| Model No.                                     | SV 9346.015                                                                                                               |
| Material                                      | Fibreglass-reinforced polyamide<br>Fire protection corresponding to UL 94-V0<br>Contact tracks: Silver-plated hard copper |
| Colour                                        | Chassis: RAL 7035<br>Cover: RAL 7001<br>Handle: RAL 7016                                                                  |
| Supply includes                               | 3 mounting hooks                                                                                                          |
| For bar systems with centre-to-centre spacing | 60 mm                                                                                                                     |
| Cable outlet                                  | Top/bottom                                                                                                                |
| Type of electrical connection                 | Screw M8                                                                                                                  |
| Rated operating current max.                  | 160 A                                                                                                                     |
| For NH size                                   | 00                                                                                                                        |
| Test specification                            | IEC/DIN EN 60 947-3<br>DIN EN 60 269-2 (fuse inserts)                                                                     |
| Dimensions                                    | Width: 50 mm<br>Height: 400 mm                                                                                            |
| Connection for round conductor cross-sections | 2.5 - 95 mm <sup>2</sup>                                                                                                  |
| To fit busbars                                | Height: 5, 10 mm                                                                                                          |
| Rated operating voltage                       | 690 V, 3~                                                                                                                 |
| Number of poles                               | 3-pole                                                                                                                    |
| Packs of                                      | 1 pc(s).                                                                                                                  |
| Weight/pack                                   | 1.36 kg                                                                                                                   |

# Features

|                              |               |
|------------------------------|---------------|
| Copper weight (kg per piece) | 0.73          |
| Customs tariff number        | 85369095      |
| EAN                          | 4028177668126 |
| ETIM 7.0                     | EC001046      |
| ECLASS 8.0                   | 27371402      |

# Approvals

|              |                                                           |
|--------------|-----------------------------------------------------------|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|-----------------------------------------------------------|