
Rittal – The System.

Faster – better – everywhere.



SV 9682.126

Partial door

State: 2026.10.30 (Source: www.rittal.com/lt-en)

SV 9682.126 - Partial door for VX

Door may be optionally hinged on the right or left.

Features

Model No.	SV 9682.126
Product description	Suitable for VX enclosures instead of a door or rear panel. The partial doors may be combined with one another as required. A trim panel is required at the top and bottom in each case. Door may be optionally hinged on the right or left. In the case of doors without viewing panel (height 600 – 1000 mm), monitor frame 2305.000 may be installed. Standard double-bit lock insert may be exchanged for lock inserts, type A.
Material	Sheet steel, 2 mm
Surface finish	Textured paint
Colour	RAL 7035
Supply includes	Partial door Cross member Hinges Lock components Assembly parts
Note	Opening angle of partial doors max. 130°
Lock	Number of locks: 2
Dimensions	Width: 1,200 mm Height: 600 mm
To fit	Width: = 1,200 mm
IP protection category to IEC 60 529	IP 54
Packs of	1 pc(s).
Net weight	14 kg
Gross weight	15.18 kg
PCF per pack (cradle-to-gate)	57.8 kg CO2 eq (Cat B)

© Rittal 2026

Features

Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
ETIM 9	EC000747
ECLASS 8.0	27182204
Product description	VX Partial door, WH: 1200x600 mm, sheet steel