

Rittal – The System.

Faster – better – everywhere.



SV 9682.142

Partial door

State: 2026.1.16 (Source: [ittal.com/it-en](https://www.ittal.com/it-en))



FRIEDHELM LOH GROUP

SV 9682.142 - Partial door for VX

Door may be optionally hinged on the right or left.

Features

| | |
|--------------------------------------|---|
| Model No. | SV 9682.142 |
| Product description | Suitable for VX enclosures instead of a door or rear panel. The partial doors may be combined with one another as required. A trim panel is required at the top and bottom in each case. Door may be optionally hinged on the right or left. In the case of doors without viewing panel (height 600 – 1000 mm), monitor frame 2305.000 may be installed. Standard double-bit lock insert may be exchanged for lock inserts, type A. |
| Material | Sheet steel, 2 mm |
| Surface finish | Textured paint |
| Colour | RAL 7035 |
| Supply includes | Partial door Cross member Hinges Lock components Assembly parts |
| Note | Opening angle of partial doors max. 130° |
| Lock | Number of locks: 1 |
| Dimensions | Width: 400 mm Height: 200 mm |
| To fit | Width: = 400 mm |
| IP protection category to IEC 60 529 | IP 54 |
| Packs of | 1 pc(s). |
| Net weight | 2.14 |
| Gross weight | 2.38 |
| PCF per pack (cradle-to-gate) | 9.3 kg CO2 eq (Cat B) |

Features

| | |
|-----------------------|--|
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94039910 |
| EAN | 4028177929005 |
| ETIM 9 | EC000747 |
| ECLASS 8.0 | 27182204 |

Approvals

| | |
|--------------|---|
| Approvals | DNV-GL Lloyds Register of Shipping UL + C-UL (listed) UL + C-UL - FTTA |
| Explanations | Declaration of conformity UK |
