
Rittal - The System.

Faster – better – everywhere.





SV 9682.167 Partial door

State: 2025.12.9 (Source: rittal.com/lt-en)



SV 9682.167 - Partial door for VX

Door may be optionally hinged on the right or left.

Features

Model No.	SV 9682.167	
Design	with viewing window	
Product description	Suitable for VX enclosures instead of a door or rear panel. The partial doors may be combined with one another as required. A trim panel is required at the top and bottom in each case. Door may be optionally hinged on the right or left. In the case of doors without viewing panel (height 600 – 1000 mm), monitor frame 2305.000 may be installed. Standard double-bit lock insert may be exchanged for lock inserts, type A.	
Material	Sheet steel, 2 mm Viewing window: Single-pane safety glass, 3 mm	
Surface finish	Textured paint	
Colour	RAL 7035	
Supply includes	Partial door Cross member Hinges Lock components Assembly parts	
Note	Opening angle of partial doors max. 130°	
Lock	Number of locks: 2	
Dimensions	Width: 600 mm Height: 600 mm	
To fit	Width: = 600 mm	
IP protection category to IEC 60 529	IP 54	
Packs of	1 pc(s).	
Net weight	7.58	

© Rittal 2025

Features

Gross weight	7.98
PCF per pack (cradle-to-gate)	30.4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
EAN	4028177928770
ETIM 9	EC000747
ECLASS 8.0	27182204

Approvals

F	Dealersties of confession in the	
Explanations	Declaration of conformity UK	

© Rittal 2025 3