



Rittal – The System.

Faster – better – everywhere.



SV 9683.664

Partial mounting plate

State: 2025.6.28 (Source: [rittal.com/lt-en](https://www.rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9683.664 - Partial mounting plate for compartment side panel

With or without duct, for direct attachment to the functional space side panel.

Features

| | |
|-------------------------------|--|
| Model No. | SV 9683.664 |
| Design | solid |
| Product description | For direct attachment to the compartment side panel for internal compartmentalisation. Universal interior installation with switchgear and controlgear. Creation of additional mounting levels. In combination with compartment dividers and side panel, internal compartmentalisation in accordance with Form 1 to 4 is possible. |
| Material | Sheet steel, 2 mm |
| Surface finish | Zinc-plated |
| Supply includes | Angle brackets and assembly parts |
| For compartment height | 400 mm |
| Dimensions | Width: 502 mm Height: 393 mm |
| To fit | Width: = 600 mm |
| Packs of | 1 pc(s). |
| Net weight | 4.72 |
| Gross weight | 5.22 |
| PCF per pack (cradle-to-gate) | 19.9 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94039910 |
| EAN | 4028177935174 |
| ETIM 9 | EC000213 |

Features

| | |
|------------|----------|
| ECLASS 8.0 | 27400613 |
|------------|----------|

Approvals

| | |
|--------------|------------------------------|
| Explanations | Declaration of conformity UK |
|--------------|------------------------------|