

Rittal – The System.

Faster – better – everywhere.



SV 9684.012

Barra E-Cu, perforada

Estado: 10/06/2026 (Fuente: rittal.com/mx-es)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL


IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9684.012 - Barra E-Cu, perforada



Características

Referencia	SV 9684.012
Descripción producto	Embarrados con taladros integrados.
Material	E-Cu F30
Longitud	1,185 mm
Normas	DIN EN 13 601
Sección	50 mm x 10 mm
Hole diameter	11.5 mm
Dimensiones	Longitud: 1.185 mm
Unidad de embalaje	1 pza(s).
Peso neto	5.34 kg
Peso bruto	5.44 kg
Contenido de cobre (kg / pza.)	5.34
Código arancelario	74071000
ETIM 9	EC001522
ECLASS 8.0	27370303
Descripción producto	SV Barra Colectora Perforada L:1185mm

Aprobaciones

Aprobaciones

UL + C-UL (listed)

Explicaciones

Declaración de conformidad UK