

**Rittal – The System.**

Faster – better – everywhere.



# undefined 1.513.0901.14 Polyamide fitting W

Staat: 7-4-2026 (Bron: [rittal.com/nl-nl](http://rittal.com/nl-nl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# undefined 1.513.0901.14 - Polyamide fitting W

Elleboogfitting van polyamide, Bescherming tegen onbedoelde ontkoppeling

## Funcities

Bestelnr.	1.513.0901.14
Uitvoering	Knie 90 graden
Product omschrijving	Haakse fitting van polyamide voor flexibele beschermingsbuizen
Voordelen	Veilig en eenvoudig losnemen met schroevendraaier
Materiaal	Polyamide O-ring: NBR
Kleur	Zwart RAL 9005
Afmetingen	Hoogte: 23 mm Lengte: 43 mm
Beschermklasse IP volgens IEC 60529	IP 54
Sleutelwijdte	19 mm
Afmetingen	Schroefdraadlengte: 8 mm
Bedrijfstemperatuurbereik	-20 °C...80 °C
Schroefdraadlengte	8 mm
Suitable for Polyamid hose DN	10 mm
Geschikt voor Ø	19 mm
Leveringseenheid	25 st.
Douanetariefnummer	39174000
Product omschrijving	SM-Hoekfitting PG9, polyamide, zwart