

Rittal – The System.

Faster – better – everywhere.



undefined 1.533.2000.50 Polyamide fitting

Staat: 1-8-2025 (Bron: rittal.com/nl-nl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



undefined 1.533.2000.50 - Polyamide fitting

Fitting van polyamide, grondstof volgens UL94, Borgmoer optioneel



Funcities

Bestelnr.	1.533.2000.50
Product omschrijving	Polyamide fitting
Voordelen	Eenvoudige montage zonder gereedschap
Materiaal	Polyamide
Kleur	RAL 7031
Afmetingen	Hoogte: 33 mm
Beschermklasse IP volgens IEC 60529	IP 55
Afmetingen	Schroefdraad: M20 Schroefdraadlengte: 13 mm
Bedrijfstemperatuurbereik	-30 °C...80 °C
Schroefdraadlengte	13 mm
Suitable for Polyamid hose DN	17 mm
Geschikt voor Ø	15,2 - 32 mm
Leveringseenheid	50 st.
Douanetariefnummer	39269097
EAN	4033878424193