

**Rittal – The System.**

Faster – better – everywhere.



# undefined 1.542.2014.51 Polyamide fitting Duo-PA

Staat: 2-5-2026 (Bron: rittal.com/nl-nl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# undefined 1.542.2014.51 - Polyamide fitting Duo-PA

Fitting van polyamide, 2 in 1 kabelwartel en buisfitting

## Funcities

Bestelnr.	1.542.2014.51
Product omschrijving	Polyamide fitting voor flexibele polyamidebuis
Voordelen	Eenvoudige montage zonder gereedschap
Materiaal	Polyamide Dichtring: NBR/FKM Afdichtingselement: NBR
Kleur	RAL 9005
Afmetingen	Hoogte: 46 mm
Kabelinvoer	Min. kabeldiameter: 7 mm Max. kabeldiameter: 12 mm
Afmetingen	Schroefdraad: M20 Schroefdraadlengte: 10 mm
Bedrijfstemperatuurbereik	-40 °C...100 °C
Schroefdraadlengte	10 mm
Suitable for Polyamid hose DN	14 mm
Geschikt voor Ø	29 mm
Leveringseenheid	50 st.
Douanetariefnummer	39269097