

**Rittal – The System.**

Faster – better – everywhere.



# undefined 1.542.2517.50 Polyamide fitting Duo-PA

Staat: 1-5-2026 (Bron: rittal.com/nl-nl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# undefined 1.542.2517.50 - Polyamide fitting Duo-PA

Fitting van polyamide, 2 in 1 kabelwartel en buisfitting

## Funcities

Bestelnr.	1.542.2517.50
Product omschrijving	Polyamide fitting voor flexibele polyamidebuis
Voordelen	Eenvoudige montage zonder gereedschap
Materiaal	Polyamide Dichtring: NBR/FKM Afdichtingselement: NBR
Kleur	RAL 9005
Afmetingen	Hoogte: 50 mm
Kabelinvoer	Min. kabeldiameter: 13 mm Max. kabeldiameter: 18 mm
Afmetingen	Schroefdraad: M25 Schroefdraadlengte: 11 mm
Bedrijfstemperatuurbereik	-40 °C...100 °C
Schroefdraadlengte	11 mm
Suitable for Polyamid hose DN	17 mm
Geschikt voor Ø	30 mm
Leveringseenheid	25 st.
Douanetariefnummer	39269097