

Rittal – The System.

Faster – better – everywhere.



undefined 1.542.3223.50 Polyamide fitting Duo-PA

Staat: 8-8-2026 (Bron: www.rittal.com/nl-nl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



undefined 1.542.3223.50 - Polyamide fitting Duo-PA

Fitting van polyamide, 2 in 1 kabelwartel en buisfitting

Funcities

Bestelnr.	1.542.3223.50
Product omschrijving	Polyamide fitting voor flexibele polyamidebuis
Voordelen	Eenvoudige montage zonder gereedschap
Materiaal	Polyamide Dichtring: NBR/FKM Afdichtingselement: NBR
Kleur	RAL 9005
Afmetingen	Hoogte: 60 mm
Kabelinvoer	Min. kabeldiameter: 18 mm Max. kabeldiameter: 24 mm
Afmetingen	Schroefdraad: M32 Schroefdraadlengte: 11 mm
Bedrijfstemperatuurbereik	-40 °C...100 °C
Schroefdraadlengte	11 mm
Suitable for Polyamid hose DN	23 mm
Geschikt voor Ø	39 mm
Leveringseenheid	25 st.
Douanetariefnummer	39269097