

Rittal – The System.

Faster – better – everywhere.



undefined 1.542.6429.70 Polyamide fitting Duo-PA

Staat: 31-7-2025 (Bron: rittal.com/nl-nl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



undefined 1.542.6429.70 - Polyamide fitting Duo-PA

Fitting van polyamide, 2 in 1 kabelwartel en buisfitting

Funcities

Bestelnr.	1.542.6429.70
Product omschrijving	Polyamide fitting voor flexibele polyamidebuis
Voordelen	Eenvoudige montage zonder gereedschap
Materiaal	Polyamide Dichtring: NBR/FKM Afdichtingselement: NBR
Kleur	RAL 9005
Afmetingen	Hoogte: 69 mm
Kabelinvoer	Min. kabeldiameter: 22 mm Max. kabeldiameter: 31 mm
Afmetingen	Schroefdraad: NPT 1½ Schroefdraadlengte: 20 mm
Bedrijfstemperatuurbereik	-40 °C...100 °C
Schroefdraadlengte	20 mm
Thread type outer thread	NPT
Suitable for Polyamid hose DN	29 mm
Geschikt voor Ø	45 mm
Leveringseenheid	10 st.
Douanetariefnummer	39269097
EAN	4033878453438