

Rittal – The System.

Faster – better – everywhere.



SZ 1.572.1460.70 Metalen fitting Pro

Staat: 31-7-2025 (Bron: rittal.com/nl-nl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 1.572.1460.70 - Metalen fitting Pro

Metal fitting for flexible conduits made of metal

Funcities

Bestelnr.	SZ 1.572.1460.70
Product omschrijving	Metalen fitting van messing
Materiaal	messing vernikkeld
Afmetingen	Hoogte: 31 mm
Beschermklasse IP volgens IEC 60529	IP 67
Afmetingen	Schroefdraad: NPT 2 Schroefdraadlengte: 10 mm
Bedrijfstemperatuurbereik	-20 °C...80 °C
Schroefdraadlengte	10 mm
Sleutelmaat grootte 2	22 mm
Geschikt voor Ø	16,5 - 24,5 mm
Leveringseenheid	50 st.
Douanetariefnummer	39269097
EAN	4033878000748