


Rittal – The System.

Faster – better – everywhere.



RX 9360.503

RiLineX Circuit-breaker component adaptor

Staat: 1-8-2025 (Bron: rittal.com/nl-nl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.503 - RiLineX Circuit-breaker component adaptor

CB component adaptors for the RiLineX busbar platform in widths 81 to 140 mm. For mounting moulded-case circuit-breakers (MCCBs). Products are available in two variants: An "Easy-Fix" variant for user-friendly external mounting of switches from all standard manufacturers, and a "Universal" variant with U nuts for maximum flexibility.

Functies

Bestelnr.	RX 9360.503
Uitvoering	Easy Fix
Voordelen	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Materiaal	Polyamide (PA 6) Vlamdovend volgens UL 94
Kleur	RAL 9005 RAL 35745
Beschermklasse IP volgens IEC 60529	IP 2XB
Nominale stroom max.	160 A
Nominale stroom (UL)	125 A
Nominale stoothoudspanning Uimp	12 kV
nominale spanning	690 V AC 690 V DC 600 V AC (UL)
Rated insulation voltage	1.000 V
Overspanningscategorie	4
Vervuilingsgraad	3

Funcities

Aantal polen	3-polig
Afgaande aansluiting	boven
Aansluiting (elektrisch)	frameklem
Geschikt voor railsysteem	RiLineX RiLine60
Frequentie van de grondgolf	50...60 Hz
Luchtvochtigheid (niet condenserend)	10...90 %
Geschikt voor railkoper	15 x 5/10 20 x 5/10 30 x 5/10
Bedrijfstemperatuurbereik	-25 °C...55 °C
Opslagtemperatuurbereik	-25 °C...75 °C
Afmetingen	Breedte: 81 mm Hoogte: 252 mm Diepte: 63 mm
Leveringseenheid	1 st.

Goedkeuringen

Goedkeuringen	UL + C-UL (listed)
---------------	--------------------