


Rittal – The System.

Faster – better – everywhere.



SZ 2433.500

Veggfestebrakett

Stat: 07.04.2026 (Kilde: rittal.com/no-no)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2433.500 - Veggfestebrakett for KL, EB, BG, AE, veggskap EL, TP overdeler og LWL-småfordelerskap

Festebrakett for stabil montering av små kapslinger og veggkapslinger.

Funksjoner

Art.nr	SZ 2433.500
Materiale	Rustfritt stål 1.4404 (AISI 316L)
Leveringsomfang	Veggfestebrakett Inkl. festemateriell
Veggavstand	10 mm
Passer for	Kapslingstype: KL EB BG AE EL
Pakkeenhet	4 stk.
Nettovekt	0,32 kg
Bruttovekt	0,299 kg
Tolltariffnummer	83025000
ETIM 9	EC002625
ETIM 8	EC002625
ECLASS 8.0	27189234
Produktbeskrivelse	SZ Veggfestebrakett, rustfritt stål, 1.4404, veggavstand 10 mm