

Rittal – The System.

Faster – better – everywhere.



VX 5301.270

Skillevegg, én del, kan skyves inn

Stat: 02.06.2026 (Kilde: rittal.com/no-no)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.270 - Skillevegg, én del, kan skyves inn for VX IT

Skillevegg for VX IT. For innskyving, hengende mellom to VX IT-skap.



Funksjoner

Art.nr	VX 5301.270
Produktbeskrivelse	For innskyving, hengende, mellom to rekkemonterte skap. Med boring Ø 40 mm i venstre og høyre hjørneområde for gjennomføring av kabler, rørledninger osv. Disse hullene kan lukkes med de vedlagte avdekningsprofilene.
Fordeler	Kan enkelt skyves inn
Materiale	Stålplate, forsinket.
Leveringsomfang	Skillevegg 2 avdekningsprofiler
Passer for	Kapslingstype: VX IT Høyde: = 2.000 mm Dybde: = 1.000 mm
Montasjetips	For innskyving av skilleveggen behøves en rekkeåpning på 3 mm
Henvisning	Bruk rekkemonteringsbrakett, utenpå, 3 mm Kan ikke brukes i kombinasjon med en pakning Ev. eksisterende pakning må fjernes før monteringen
Kapslingsgrad IP iht. IEC 60 529	IP 20 (bei montierten Abdeckkappen)
Pakkeenhet	1 stk.
Nettovekt	27 kg
Bruttovekt	27,5 kg

Funksjoner

PCF/VE (Cradle-to-Gate)	104,8 kg CO2 eq (Cat B)
Merknad som gjelder PCF-klasse	Kategori B: PCF-verdi (Cradle-to-Gate) omtrentlig beregnet på grunnlag av produktets vekt og selvdeklart
Tolltariffnummer	94039910
ETIM 9	EC002525
ECLASS 8.0	27189234
Produktbeskrivelse	VX IT skilleplate kan settes i ett stykke, HxD: 2000x1000, stålplate