



VX 8617.110 - Systemchassis 23 x 64 mm For VX, VX IT, VX SE, AX-plast

For variabel og individuell innvendig utbygging av skaprammen på det innvendige montasjenivået og for montering i kompaktapparatsskap.



Funksjoner

Art.nr	VX 8617.110
Produktbeskrivelse	For variabel og individuell innvendig utbygging av skaprammen på det innvendige montasjenivået og for montering i kompaktapparatsskap.
Fordeler	Hektes enkelt inn i systemhullene og sikres Systemhull på alle fire sider Hull oppe og nede for burmuttere for feste av egne komponenter med metriske skruer
Materiale	Stålplate
Overflate	Forsinket
Leveringsomfang	Inkl. festemateriell
Monteringsmuligheter VX	In enclosure width/depth 400 mm on the inner mounting level
Montasjemuligheter VX SE	In enclosure depth 400 mm, on the inner mounting level, in conjunction with adaptor rail for VX compatibility
Monteringsmuligheter AX	In enclosure width/height 400 mm, in conjunction with rail for interior installation AX and base configuration rail for AX

Funksjoner

Monteringsmuligheter, AX rustfritt stål	I kapslingsbredde 400 mm, i forbindelse med bunn utbyggingsskinne
Monteringsmuligheter, AX-plast	In enclosure width 400 mm, in conjunction with universal bracket
Monteringsmuligheter CX	I pultunderdel i kapslingsdybde 400 mm I styrepult underdel i husdybde 400 mm
Montasjemuligheter VX sokkel	I sokkelbredde/-dybde 400 mm på sokkelpanelene, i forbindelse med sokkelutbyggingvinkel
Passer for	Kapslingstype: VX VX IT VX SE AX AX-plast Suitable for width or height or depth: 400 mm
Passer for	Sokkelsystem VX
Pakkeenhet	4 stk.
Nettovekt	1,4 kg
Bruttovekt	1,53 kg
PCF/VE (Cradle-to-Gate)	8,39
Tolltariffnummer	73269098
ETIM 9	EC002620
ECLASS 8.0	27189234
Produktbeskrivelse	VX systemchassis 23 x 64 mm, for innvendig montasjenivå, for B/H/D: 400 mm

Godkjenninger

Forklaringer	PCF-declaration
--------------	-----------------