

**Rittal – The System.**

Faster – better – everywhere.



**SV 9614.000**

**Mini-PLS Apparatadapter**

Stat: 04.07.2026 (Kilde: [rittal.com/no-no](http://rittal.com/no-no))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9614.000 - Mini-PLS Apparatadapter

Maks. målestrøm fra 12 A til 100 A.

## Funksjoner

Art.nr	SV 9614.000
Materiale	polyamid Brannsikkerhet iht. UL 94-V0
Farge	RAL 7035
Tilkoblingsledninger (AWG)	AWG 12
Måledriftsspenning	690 V, 3~
Driftsstrøm maks.	25 A
Dimensjoner	Bredde: 54 mm Høyde: 160 mm
Bæreskiner antall/høyde	1 / 7,5 mm
Egnet for produsent (type)	ABB Eaton Siemens MS325 MS450 max. 25 A MS451 max. 25 A PKZM4 bis 25 A PKE65 bis 25 A 3RV10 31 bis 25 A
Pakkeenhet	1 stk.
Nettovekt	0,27 kg
Bruttovekt	0,318 kg
Kobberandel (kg / stk.)	0,041
Tolltariffnummer	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304

# Funksjoner

---

Produktbeskrivelse	SV Mini-PLS apparatadapter, 25 A, 690 V, 3-polet, tilkoblingsledning AWG 12, BH: 54x160 mm, DIN-skiner H: 7,5 mm
--------------------	--

# Godkjenninger

---

Godkjenninger	UR + C-UR (recognized)
---------------	------------------------

---

Forklaringer	Samsvarserklæring Samsvarserklæring UK
--------------	---