

**Rittal – The System.**

Faster – better – everywhere.



# SV 9614.100

## Mini-PLS Apparatadapter

Stat: 10.06.2026 (Kilde: [rittal.com/no-no](http://rittal.com/no-no))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9614.100 - Mini-PLS Apparatadapter

Maks. målestrøm fra 12 A til 100 A.

## Funksjoner

Art.nr	SV 9614.100
Materiale	polyamid Brannsikkerhet iht. UL 94-V0
Farge	RAL 7035
Tilkoblingsledninger (AWG)	AWG 12
Måledriftsspenning	690 V, 3~
Driftsstrøm maks.	25 A
Dimensjoner	Bredde: 45 mm Høyde: 160 mm
Bæreskiner antall/høyde	1 / 7,5 mm
Egnet for produsent (type)	ABB Eaton Schneider Electric Siemens MS116 PKZM0 bis 25 A PKZM01 bis 25 A PKE12 PKE32 bis 25 A GV2-P bis 25 A GV2-RT GV2-LE10 GV3 bis 25 A 3RV10 21 3RV20 21 bis 25 A 3RV10 11 3RV20 11
Pakkeenhet	1 stk.
Nettovekt	0,25 kg

## Funksjoner

---

Bruttovekt	0,29 kg
Kobberandel (kg / stk.)	0,041
Tolltariffnummer	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Produktbeskrivelse	SV Mini-PLS apparatadapter, 25 A, 690 V, 3-polet, tilkoblingsledning AWG 12, BH: 45x160 mm, DIN-skiner H: 7,5 mm

## Godkjenninger

---

Godkjenninger	UR + C-UR (recognized)
Forklaringer	Samsvarserklæring Samsvarserklæring UK