

# Rittal – The System.

Faster – better – everywhere.



## SV 9615.100 Mini-PLS Apparatadapter

Stat: 01.05.2026 (Kilde: [rittal.com/no-no](http://rittal.com/no-no))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9615.100 - Mini-PLS Apparatadapter

Maks. målestrøm fra 12 A til 100 A.

## Funksjoner

Art.nr	SV 9615.100
Materiale	polyamid Brannsikkerhet iht. UL 94-V0
Farge	RAL 7035
Tilkoblingsledninger (AWG)	AWG 12
Måledriftsspenning	690 V, 3~
Driftsstrøm maks.	25 A
Dimensjoner	Bredde: 45 mm Høyde: 160 mm
Bæreskinner antall/høyde	1 / 15 mm
Pakkeenhet	1 stk.
Nettvekt	0,29 kg
Bruttovekt	0,329 kg
Kobberandel (kg / stk.)	0,041
Tolltariffnummer	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Produktbeskrivelse	SV Mini-PLS apparatadapter, 25 A, 690 V, 3-polet, tilkoblingsledning AWG 12, BH: 45x160 mm, DIN-skinner H: 15 mm

## Godkjenninger

Godkjenninger	UR + C-UR (recognized)
---------------	------------------------

# Godkjenninger

---

Forklaringer

Samsvarserklæring

Samsvarserklæring UK