Rittal - The System.

Faster – better – everywhere.





AX 1260.000 Basic enclosure AX, sheet steel

State: 4/11/2025 (Source: rittal.com/nz-en)



AX 1260.000 - Basic enclosure AX, sheet steel

The compact enclosure AX with integral enclosure locators in the roof, base and side forms the familiar 25 mm system pitch pattern from the VX25 large enclosure. With this unique, patented system, AX compact enclosures are prepared for all types of configurations and refits. System components and accessories are easily, quickly and securely installed and retrofitted on rails, with no drilling required.







Features

Model No.	AX 1260.000
Benefits	More interior installation options thanks to integral enclosure locators on a 25 mm system pitch pattern combined with the interior installation rail and our diverse range of system accessories Maintains the protection category (UL approval) by mounting the interior installation rail with no drilling required. Base configuration rail provides additional mounting level and increased load capacity Simple planning and configuration with the Rittal RiPanel configurator
Material	Enclosure: Sheet steel Door: Sheet steel, all-round foamed-in PU seal
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
Colour	RAL 7035

© Rittal 2025 2

Features

Supply includes	Enclosure with door(s)
	Gland plate(s) in enclosure base
	Mounting plate
	Perforated door strip
	Lock: 3 mm double-bit
Protection category NEMA	NEMA 1
	NEMA 3R
	NEMA 4
	NEMA 12
Protection category to IEC 60 529	IP 66
Type rating to UL 50E	Type 1
	Type 3R
	Type 4
	Type 12
IK Code	IK10
Dimensions	Width: 600 mm
	Height: 1,200 mm
	Depth: 300 mm
Material thickness - door	2 mm
Material thickness - enclosure	1.5 mm
Material thickness of mounting	2.5 mm
plate	
Dimensions mounting plate (W x	545 mm x 1,175 mm
H)	
Number of doors	1
Interchangeable door hinge	Yes
Lock	Lock version: 3-point lock system
	Number of locks: 1
	Lock insert: 3 mm double-bit
Gland plate	Size: 7
- I	Qty.: 1
	••
Dania mantanial	Chart at al
Basic material	Sheet steel

© Rittal 2025 3

Features

Net weight	45.4
Gross weight	50
PCF per pack (cradle-to-gate)	156.9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94032080
EAN	4028177813274
E-Number Sweden	E3465165
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Approvals	Bureau Veritas
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Manufacturer's declaration
	Declaration of conformity
	Declaration of conformity UK
	PCF-declaration

© Rittal 2025