

# Rittal – The System.

Faster – better – everywhere.



## BG 1578.560

### Bus enclosures BG

State: 25/08/2025 (Source: [rittal.com/nz-en](https://www.rittal.com/nz-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# BG 1578.560 - Bus enclosures BG

Wall-mounted enclosure with door of sheet steel, with polycarbonate viewing window. Protection category IP 65. Bus modules of virtually all makes may be attached.

## Features

|                                   |  |
|-----------------------------------|--|
| Model No.                         | BG 1578.560  |
| Material                          | Enclosure: Sheet steel<br>Door: Sheet steel<br>Viewing window: Polycarbonate, 4 mm   |
| Surface finish                    | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint   |
| Colour                            | RAL 7035   |
| Supply includes                   | Enclosure with door<br>Viewing window in the door<br>Mounting plate<br>Gland plate in enclosure base                         |
| Protection category NEMA          | NEMA 12  |
| Protection category to IEC 60 529 | IP 65  |
| IK Code                           | IK08   |
| Dimensions                        | Width: 600 mm<br>Height: 300 mm<br>Depth: 155 mm   |
| Dimensions mounting plate (W x H) | 585 mm x 275 mm  |
| Visible area                      | Viewing window width: 540 mm<br>Viewing window height: 190 mm<br>Distance bottom edge of window - bottom edge of door: 42 mm |
| Material thickness - enclosure    | 1.38 mm  |
| Material thickness - door         | 1.25 mm  |
| Door hinge position               | bottom   |

## Features

|                       |   |
|-----------------------|---|
| Lock                  | Lock version: Cam<br>Number of locks: 2<br>Lock insert: 3 mm double-bit |
| Basic material        | Sheet steel   |
| Packs of              | 1 pc(s).  |
| Net weight            | 9.352   |
| Gross weight          | 9.844   |
| Customs tariff number | 94032080  |
| EAN                   | 4028177262140   |
| ECLASS 8.0            | 27180101  |

## Approvals

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |